

CLT.10.2157 Cut Sheet



SapiSelco CLICK Tie series low temperature beaded releasable cable tie, 25.31in length, 0.22in width, 61.82lb tensile strength, 7.08in maximum bundle diameter, red, low-density polyethylene (LDPE). Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CLT.10.2157>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	Low temperature beaded releasable
Series	CLICK Tie
Length	25.31in
Width	0.22in
Tensile Strength	61.82lb
Maximum Bundle Diameter	7.08in
Color	Red
Material	Low-density polyethylene (LDPE)
Temperature Rating	-58 to +140 deg F
Quantity per Pack	100

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document