

# CMV-ACC02 Cut Sheet



NITRA solenoid valve cable, 25-pin female D-sub to pigtail, 45-degree cable entry, 28 AWG, IP65, 8.2ft/2.5m cable length. For use with CMV series solenoid valves.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CMV-ACC02>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Cable
<b>Cable Type</b>	Solenoid valve
<b>Connection 2</b>	Pigtail
<b>Cable Entry</b>	45-degree
<b>Conductor Size</b>	28 AWG
<b>IP Rating</b>	IP65
<b>Cable Length</b>	8.2ft/2.5m
<b>For Use With</b>	CMV series solenoid valves

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>