

CMV-ACC03 Cut Sheet



NITRA solenoid valve cable, 25-pin female D-sub to pigtail, 45-degree cable entry, 28 AWG, IP65, 16.4ft/5m cable length. For use with CMV series solenoid valves.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CMV-ACC03>

Technical Specifications

Brand	NITRA
Item	Cable
Cable Type	Solenoid valve
Connection 2	Pigtail
Cable Entry	45-degree
Conductor Size	28 AWG
IP Rating	IP65
Cable Length	16.4ft/5m
For Use With	CMV series solenoid valves

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document