

CMV-ACC11 Cut Sheet



NITRA connector, 25-pin female D-sub, 45-degree cable entry, 22-18 AWG, accepts cable diameter size 0.19-0.39in, IP65. For use with CMV series solenoid valves.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CMV-ACC11>

Technical Specifications

Brand	NITRA
Item	Connector
Connector Type	25-pin female D-sub
Cable Entry	45-degree
Conductor Size	22-18 AWG
Cable Diameter Size	0.19-0.39in
IP Rating	IP65
For Use With	CMV series solenoid valves

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CMV-ACC11.pdf>
See store item page for other formats.