

# CMV-B3L-1A Cut Sheet



NITRA solenoid valve, compact modular, 5-way, 3-position, center closed, double solenoid, reinforced technopolymer body, IP65, locking manual override, (2) 5/32in (4mm) PTC tubing outlet(s), Cv=0.2, 24 VDC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CMV-B3L-1A>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Series</b>	Compact modular valves (CMV)
<b>Item</b>	Valve
<b>Working Fluid</b>	Air
<b>Valve Type</b>	Solenoid directional control
<b>Port Quantity</b>	5-way
<b>Number Of Positions</b>	3
<b>Valve Configuration</b>	Center closed
<b>Action</b>	Double solenoid
<b>Body Material</b>	Reinforced technopolymer
<b>IP Rating</b>	IP65
<b>Outlet Port</b>	(2) 5/32in (4mm) push-to-connect tubing
<b>Manual Override Type</b>	Locking
<b>Flow Coefficient</b>	0.2
<b>Operating Voltage</b>	24 VDC
<b>Indicating Type</b>	LED indication
<b>Form Factor</b>	Compact modular
<b>Requires</b>	One CMV series left end plate and right end plate for any combination of one to sixteen solenoids
<b>Additional Information</b>	Valve uses two of the available 16 wiring positions on the inlet plate

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>