

# CMV-C2X-4X Cut Sheet



NITRA pneumatic modular plate, left supply/exhaust end, Cv=12.4, (2) 3/8in push-to-connect tubing inlet(s), 3/8in female NPT exhaust(s), 5/32in (4mm) push-to-connect tubing pilot(s), anodized aluminum body, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CMV-C2X-4X>

## Technical Specifications

Brand	NITRA
Item	Modular plate
Working Fluid	Pneumatic
Pneumatic Function	Left supply/exhaust end
Flow Coefficient	12.4
Inlet Port	(2) 3/8in push-to-connect tubing
Exhaust Port	3/8in female NPT
Pilot Port	5/32in (4mm) push-to-connect tubing
Body Material	Anodized aluminum
IP Rating	IP65
Electrical Connection	25-pin male D-sub
For Use With	CMV series solenoid valves
Requires	CMV series 25-pin female D-sub control cable

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>