

COPC2PB Cut Sheet



AttaBox Commander series pushbutton enclosure, 2 holes, 30mm, NEMA 1/3R/4X/6P/12, 5 x 3 x 3in (HxWxD), wall mount, polycarbonate, light gray, gloss finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/COPC2PB>

Technical Specifications

Brand	AttaBox
Item	Pushbutton enclosure
Series	Commander
Number of Pushbutton Holes	2 holes
Pushbutton Hole Nominal Size	30mm
Slope Top	No
NEMA Rating	1/3R/4X/6P/12
IP Rating	IP68
Nominal Enclosure Dimensions	5 x 3 x 3in (HxWxD)
Enclosure Height	5.12in
Enclosure Width	3.16in

Enclosure Depth	3.54in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	Polycarbonate
Color	Light gray
Finish	Gloss
Cover Type	Screw cover
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E319779
UL Recognized File #	none
UL Hazardous File #	none
CE	View CE declarations
CSA File #	LR069014
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/COPC2PB.pdf>
See store item page for other formats.