


CPSB-123-240-24 Cut Sheet



LUTZE CPS Universal series switching power supply, 24 VDC @ 10A/240W, 220/480 VAC nominal input, 1, 2 and 3-phase, enclosed, aluminum housing, 35mm DIN rail mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CPSB-123-240-24>

Technical Specifications

Brand	LUTZE
Item	Power supply
Series	CPS Universal
Power Supply Type	Switching
Efficiency	93% @240VAC
Output Configuration	Single output
Output	220/480 VAC @ 10A/240W
Output Voltage Range	23-28 VDC
Input voltage range	187-550 VAC/250-725 VDC
Input Voltage Selection Type	Automatic
Number of Input Phases	1, 2 and 3
Protection Type(s)	<ul style="list-style-type: none">• overvoltage• overcurrent• short circuit• over-temperature

Remote On/Off	No
Enclosure Type	Enclosed
Housing Material	Aluminum
IP Rating	IP20
Mounting	35mm DIN rail
Connector Type	Screw terminals
Integrated UPS Battery Control	No
Operating Temperature	-40 to +70 deg C
Power Boost	150% for 5s

Agency Approvals

UL Listed File #	E249179
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/CPSB-123-240-24.pdf>
See store item page for other formats.