

CR6022-C500-C298 Cut Sheet



Code barcode scanner, 1D, 2D and DPM, imager, corded, USB, rugged duty, dual 960 x 640 optical resolution. 6ft USB cable included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CR6022-C500-C298>

Technical Specifications

Brand	Code
Item	Barcode scanner
Form Factor	Handheld
Scanner Capability	1D, 2D and DPM
Scanner Type	Imager
Connectivity	Corded
Connection	USB
Duty Rating	Rugged duty
Optical Resolution	Dual 960 x 640
Decode Capability	<ul style="list-style-type: none">• 1D: BC412, Codabar, Code 11, Code 32, Code 39, Code 93, Code 128, IATA 2 of 5, Interleaved 2 of 5, GS1 DataBar, Hong Kong 2 of 5, Matrix 2 of 5, MSI Plessey, NEC 2 of 5, Pharmacode, Plessey, Straight 2 of 5, Telepen, Trioptic, UPC/EAN/JAN• Stacked 1D: Codablock F, Code 49, GS1 Composite (CC-A/CC-B/CC-C), MicroPDF, PDF417• 2D: Aztec Code, Data Matrix, Data Matrix Rectangular Extension, Grid Matrix, Han Xin, Maxicode, Micro QR Code, QR Code, QR Model 1• Postal: Australian Post, Canada Post, Intelligent Mail, Japan Post, KIX Code, Korea Post, Planet, Post-net, UK Royal Mail, UPU ID-tags
Field Of View	51 degree horizontal by 39.4 degree vertical
Shock Rating	Multiple drops of 6ft on concrete
IP Rating	IP54
Operating Temperature	-20 to +50 deg C (-4 to 122 deg F)
Includes	6ft USB cable

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document