

# CR950-K302-C298 Cut Sheet



Code barcode scanner, 1D and 2D, imager, corded, RS-232, general duty, 1280 x 960 optical resolution. 6ft RS-232 cable and power supply included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CR950-K302-C298>

## Technical Specifications

<b>Brand</b>	Code
<b>Item</b>	Barcode scanner
<b>Form Factor</b>	Handheld
<b>Scanner Capability</b>	1D and 2D
<b>Scanner Type</b>	Imager
<b>Connectivity</b>	Corded
<b>Connection</b>	RS-232
<b>Duty Rating</b>	General duty
<b>Optical Resolution</b>	1280 x 960
<b>Decode Capability</b>	<ul style="list-style-type: none"><li>• 1D: BC412, Codabar, Code 11, Code 32, Code 39, Code 93, Code 128, IATA 2 of 5, Interleaved 2 of 5, GS1 DataBar, Hong Kong 2 of 5, Matrix 2 of 5, MSI Plessey, NEC 2 of 5, Plessey, Straight 2 of 5, Telepen, Trioptic, UPC/EAN/JAN</li><li>• Stacked 1D: GS1 Composite (CC-A/CC-B/CC-C), MicroPDF, PDF417</li><li>• 2D: Aztec Code, Data Matrix, Data Matrix Rectangular Extension, Micro QR Code, QR Code, QR Model 1</li></ul>

<b>Field Of View</b>	51 degree horizontal by 39.4 degree vertical
<b>Shock Rating</b>	Multiple drops of 6ft on concrete
<b>IP Rating</b>	IP54
<b>Operating Temperature</b>	-20 to +50 deg C (-4 to 122 deg F)
<b>Includes</b>	6ft RS-232 cable and power supply

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/CR950-K302-C298.pdf>  
See store item page for other formats.