

CS10HMODU-C16-0A60 Cut Sheet



Captron Caneo Series10 Hygienic capacitive pushbutton sensor switch, IP69K, 22mm, static, stainless steel bezel, semi-automatic LED control, Operator: white, 32.4mm, operator text "power symbol", white.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CS10HMODU-C16-0A60>

Technical Specifications

Brand	Captron
Item	Capacitive pushbutton sensor switch
Series	Caneo Series10 Hygienic
IP Rating	IP69K
Barrel Size	22mm
Action	Static
Bulb Type	LED illuminated
Output	PNP, N.O.
Contact Type	(1) N.O.
Light Color(s)	Green/red
LED Control	Semi-automatic
Base Material	Stainless steel
Bezel Material	Stainless steel
Bezel Color	Silver
Operator Color	White
Operator Type	Flush

Operator Size	32.4mm
Operator Shape	Round
Operator Material	Polycarbonate
Operator Legend	Power symbol
Text Color	White
Voltage Rating	24 VDC
Voltage Regulation	Full voltage
Communication Port and Connection Type(s)	(1) 5-wire pigtail (IO-Link)
Port Protocol(s)	IO-Link Class A Device
Port Speed(s)	IO-Link COM2
IO-Link Version	IO-Link v1.1
Standard I/O Mode Supported	Yes
Application	Suitable for food and beverage applications, FDA compliant

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	80010178
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/CS10HMODU-C16-0A60.pdf>
See store item page for other formats.