

CS16166 Cut Sheet



Hammond enclosure, NEMA 1, 16 x 16 x 6in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CS16166>

Technical Specifications

Brand	Hammond
Item	Enclosure
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	1
IP Rating	IP20
Nominal Enclosure Dimensions	16 x 16 x 6in (HxWxD)
Enclosure Height	16.00in
Enclosure Width	16.00in
Enclosure Depth	6.06in
Mounting	Wall

Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Screw cover
Shelf	No
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LR21001
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CS16166.pdf>
See store item page for other formats.