

CS60-BM38-EP15/300ID Cut Sheet



di-soric CS60 series 2D vision camera, 50-515mm operating distance, localization, detection, counting and read code, 1440 x 1080 resolution, white and red light emission, TCP/IP, FTP Client, SFTP Client, Profinet Client and EtherNet/IP Client, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CS60-BM38-EP15/300ID>

Technical Specifications

Brand	di-soric	Light Emission	White and red
Series	CS60	Input	(3) NPN or PNP
Item	2D vision camera	Output	(5) NPN or PNP
Operating Distance	50-515mm	IP Rating	IP67
Lens Mount	S-mount	Housing Material	Die-cast zinc
Focus Type	Manual	Housing Size	34 x 45 x 98mm body
Shutter Type	Global	Operating Voltage	18-30 VDC
Inspection Tools	Localization, detection, counting and read code	Operating Temperature	0 to 50 deg C
Decode Capability	Code 2 of 5, Codabar, Code 128, Code 39, Databar, UPC / EAN, Pharmacode, Aztec Code, Data Matrix, Dotcode, QR, PDF 417	Connection	(1) 12-pin M12 quick-disconnect and (1) 4-pin M12 X-coded
Response Time	30fps	Port Protocol(s)	TCP/IP, FTP Client, SFTP Client, Profinet Device and EtherNet/IP Client
Resolution	1440 x 1080	Includes	O-S1-S-080-40 lens and CS60-WINDOW
Sensor Size	1/2.9in	Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E303138
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/CS60-BM38-EP15_300ID.pdf
See store item page for other formats.