

# CS60-BM38-EP15/300 Cut Sheet



di-soric CS60 series 2D vision camera, 50-515mm operating distance, localization, detection and counting, 1440 x 1080 resolution, white and red light emission, TCP/IP, FTP Client, SFTP Client, Profinet Client and EtherNet/IP Client, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CS60-BM38-EP15/300>

## Technical Specifications

<b>Brand</b>	di-soric
<b>Series</b>	CS60
<b>Item</b>	2D vision camera
<b>Operating Distance</b>	50-515mm
<b>Lens Mount</b>	S-mount
<b>Focus Type</b>	Manual
<b>Shutter Type</b>	Global
<b>Inspection Tools</b>	Localization, detection and counting
<b>Response Time</b>	30fps
<b>Resolution</b>	1440 x 1080
<b>Sensor Size</b>	1/2.9in
<b>Light Emission</b>	White and red
<b>Input</b>	(3) NPN or PNP

<b>Output</b>	(5) NPN or PNP
<b>IP Rating</b>	IP67
<b>Housing Material</b>	Die-cast zinc
<b>Housing Size</b>	34 x 45 x 98mm body
<b>Operating Voltage</b>	18-30 VDC
<b>Operating Temperature</b>	0 to 50 deg C
<b>Connection</b>	(1) 12-pin M12 quick-disconnect and (1) 4-pin M12 X-coded
<b>Port Protocol(s)</b>	TCP/IP, FTP Client, SFTP Client, Profinet Device and EtherNet/IP Client
<b>Includes</b>	O-S1-S-080-40 lens and CS60-WINDOW
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E303138
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
[https://cdn.automationdirect.com/static/drawings/2d/CS60-BM38-EP15\\_300.pdf](https://cdn.automationdirect.com/static/drawings/2d/CS60-BM38-EP15_300.pdf)  
See store item page for other formats.