

CS60-BM38-EP15/400ID Cut Sheet



di-soric CS60 series 2D vision camera, 50-515mm operating distance, localization, detection, counting, read code, and measurement, 1440 x 1080 resolution, white and red light emission, TCP/IP, FTP Client, SFTP Client, Profinet Client and EtherNet/IP Client, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CS60-BM38-EP15/400ID>

Technical Specifications

Brand	di-soric
Series	CS60
Item	2D vision camera
Operating Distance	50-515mm
Lens Mount	S-mount
Focus Type	Manual
Shutter Type	Global
Inspection Tools	Localization, detection, counting, read code, and measurement
Decode Capability	Code 2 of 5, Codabar, Code 128, Code 39, Databar, UPC / EAN, Pharmacode, Aztec Code, Data Matrix, Dotcode, QR, PDF 417
Response Time	30fps
Resolution	1440 x 1080
Sensor Size	1/2.9in

Light Emission	White and red
Input	(3) NPN or PNP
Output	(5) NPN or PNP
IP Rating	IP67
Housing Material	Die-cast zinc
Housing Size	34 x 45 x 98mm body
Operating Voltage	18-30 VDC
Operating Temperature	0 to 50 deg C
Connection	(1) 12-pin M12 quick-disconnect and (1) 4-pin M12 X-coded
Port Protocol(s)	TCP/IP, FTP Client, SFTP Client, Profinet Device and EtherNet/IP Client
Includes	O-S1-S-080-40 lens and CS60-WINDOW
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E303138
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/CS60-BM38-EP15_400ID.pdf
See store item page for other formats.