

CSG24246 Cut Sheet



Hammond enclosure, NEMA 1, 24 x 24 x 6in (HxWxD), wall mount, galvanized steel, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CSG24246>

Technical Specifications

Brand	Hammond
Item	Enclosure
Slope Top	No
NEMA Rating	1
IP Rating	IP20
Nominal Enclosure Dimensions	24 x 24 x 6in (HxWxD)
Enclosure Height	24.00in
Enclosure Width	24.00in
Enclosure Depth	6.06in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	Galvanized steel
Cover Type	Screw cover
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LR21001
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document