

# CSMS5A5CY1602 Cut Sheet



Cordset cable, 7/8in-16 UN thread axial female to pigtail, 5-pole, PVC jacket, yellow, 6.5ft/2m cable length, IP68, sensor & signal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CSMS5A5CY1602>

---

## Technical Specifications

<b>Item</b>	Cable
<b>Cable Type</b>	Cordset
<b>Connection 1</b>	7/8in-16 UN thread axial female
<b>Connection 2</b>	Pigtail
<b>Number of Poles</b>	5
<b>Jacket Material</b>	PVC
<b>Jacket Color</b>	Yellow
<b>Cable Length</b>	6.5ft/2m
<b>IP Rating</b>	IP68
<b>Application</b>	Sensor & signal

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>