


# CT-007-048-24-0 Cut Sheet



BLOCK control transformer, open core, 75 VA, 1-phase, 240/480 VAC, 24 VAC secondary, 50/60 Hz, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CT-007-048-24-0>

## Technical Specifications

<b>Brand</b>	BLOCK
<b>Series</b>	CT
<b>Item</b>	Transformer
<b>Transformer Type</b>	Control
<b>Core Type</b>	Open
<b>Power Rating</b>	75 VA
<b>Number of Phases</b>	1
<b>Primary Voltage</b>	240/480 VAC
<b>Secondary Voltage</b>	24 VAC
<b>Frequency</b>	50/60 Hz
<b>Fused</b>	No
<b>Electrostatic Shield</b>	No
<b>Mounting</b>	Panel
<b>Connection</b>	Screw terminals

## Agency Approvals

<b>UL Recognized File #</b>	E103521 Displayed as Type/Model EI
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/CT-007-048-24-0.pdf>  
See store item page for other formats.