

# CTF-0150-5-SA Cut Sheet



AcuAMP AC current transformer, split core, 150A primary, 5A secondary, 1.19 x 2.22in sensing window, 1.5% accuracy, screw terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CTF-0150-5-SA>

## Technical Specifications

<b>Brand</b>	AcuAMP
<b>Item</b>	Transformer
<b>Transformer Type</b>	Current
<b>Voltage Type</b>	AC
<b>Body Type</b>	Split core
<b>Primary Current</b>	150A
<b>Secondary Current</b>	5A
<b>Sensing Window</b>	1.19 x 2.22in
<b>Accuracy</b>	1.5%
<b>Secondary Conductors</b>	22-14 AWG copper only
<b>Secondary Connection Type</b>	Screw terminal
<b>Mounting</b>	Pass-through conductor

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E488023
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/CTF-0150-5-SA.pdf>  
See store item page for other formats.