

# CTF-1000-5-SB Cut Sheet



AcuAMP AC current transformer, split core, 1000A primary, 5A secondary, 2.36 x 3.49in sensing window, 1% accuracy, screw terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CTF-1000-5-SB>

## Technical Specifications

Brand	AcuAMP
Item	Transformer
Transformer Type	Current
Voltage Type	AC
Body Type	Split core
Primary Current	1000A
Secondary Current	5A
Sensing Window	2.36 x 3.49in
Accuracy	1%
Secondary Conductors	22-14 AWG copper only
Secondary Connection Type	Screw terminal
Mounting	Pass-through conductor

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E488023
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/CTF-1000-5-SB.pdf>  
See store item page for other formats.