

CTF-1000-5-SB Cut Sheet



AcuAMP AC current transformer, split core, 1000A primary, 5A secondary, 2.36 x 3.49in sensing window, 1% accuracy, screw terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CTF-1000-5-SB>

Technical Specifications

| | |
|----------------------------------|------------------------|
| Brand | AcuAMP |
| Item | Transformer |
| Transformer Type | Current |
| Voltage Type | AC |
| Body Type | Split core |
| Primary Current | 1000A |
| Secondary Current | 5A |
| Sensing Window | 2.36 x 3.49in |
| Accuracy | 1% |
| Secondary Conductors | 22-14 AWG copper only |
| Secondary Connection Type | Screw terminal |
| Mounting | Pass-through conductor |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E488023 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |