

# CTF-5RL-0100 Cut Sheet



AcuAMP AC current transformer, solid core, 100A primary, 5A secondary, 1.56in diameter sensing window, 2% accuracy, (2) 24in 16AWG lead wires.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CTF-5RL-0100>

## Technical Specifications

Brand	AcuAMP
Item	Transformer
Transformer Type	Current
Voltage Type	AC
Body Type	Solid core
Primary Current	100A
Secondary Current	5A
Sensing Window	1.56in diameter
Accuracy	2%
Secondary Connection Type	(2) 24in 16AWG lead wires
Mounting	Pass-through conductor

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E488023
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/CTF-5RL-0100.pdf>  
See store item page for other formats.