

# CTF-5RL-0100 Cut Sheet



AcuAMP AC current transformer, solid core, 100A primary, 5A secondary, 1.56in diameter sensing window, 2% accuracy, (2) 24in 16AWG lead wires.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CTF-5RL-0100>

## Technical Specifications

<b>Brand</b>	AcuAMP
<b>Item</b>	Transformer
<b>Transformer Type</b>	Current
<b>Voltage Type</b>	AC
<b>Body Type</b>	Solid core
<b>Primary Current</b>	100A
<b>Secondary Current</b>	5A
<b>Sensing Window</b>	1.56in diameter
<b>Accuracy</b>	2%
<b>Secondary Connection Type</b>	(2) 24in 16AWG lead wires
<b>Mounting</b>	Pass-through conductor

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E488023
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>