

CTF-7RL-0800 Cut Sheet



AcuAMP AC current transformer, solid core, 800A primary, 5A secondary, 2.5in diameter sensing window, 1% accuracy, (2) 24in 16AWG lead wires.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CTF-7RL-0800>

Technical Specifications

Brand	AcuAMP
Item	Transformer
Transformer Type	Current
Voltage Type	AC
Body Type	Solid core
Primary Current	800A
Secondary Current	5A
Sensing Window	2.5in diameter
Accuracy	1%
Secondary Connection Type	(2) 24in 16AWG lead wires
Mounting	Pass-through conductor

Agency Approvals

UL Listed File #	None
UL Recognized File #	E488023
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document