

# CTS12 Cut Sheet



MK Morse hole cutter, 3/4in (19mm), carbide tipped steel, straight pitch, 3/16in (4.5mm) maximum cutting depth.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CTS12>

## Technical Specifications

Brand	MK Morse
Item	Hole cutter
Hole Saw Size	3/4in (19mm)
Maximum Cutting Depth	3/16in (4.5mm)
Material	Carbide tipped steel
Hardened Steel Backer	No
Tooth Density	3 teeth/in

Toothing	Straight pitch
Cutting Direction	Right hand
For Use On	Steel, stainless steel, aluminum, wood, plastic and composite
Application	Hole cutting
Additional Information	Integrated ejector spring for quick slug removal

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>