

CTT-AN-D24 Cut Sheet



AutomationDirect multi-function digital counter/timer/tachometer, two-line, 6-digit, two-color LCD, fully selectable timing range, 24 VDC operating voltage, (1) concurrent NPN transistor and SPST relay and (1) NPN transistor output(s), 1/16 DIN mount, screw terminal(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CTT-AN-D24>

Technical Specifications

| | |
|-----------------------------|--|
| Brand | AutomationDirect |
| Item | Multi-function digital counter/timer/tachometer |
| Display Type | Two-line, 6-digit, two-color LCD |
| Timing Range | Fully selectable |
| Operating Voltage | 24 VDC |
| Timer Output Type(s) | (1) concurrent NPN transistor and SPST relay and (1) NPN transistor |
| Timer Function(s) | <ul style="list-style-type: none">• signal on-delay 1• signal on-delay 2• signal off-delay• signal on• power on-delay• power on-delay hold• repeat cycle• repeat cycle 2• repeat cycle hold• signal cumulate• signal twin on-start• signal twin off-start |

| | |
|-----------------------|--|
| Mounting | 1/16 DIN |
| Connector Type | Screw terminal(s) |
| Includes | Panel mounting clip |
| Application | Operates in one of four modes (selectable) - Counter (5 functions), Timer (12 functions), mixed Timer + Counter, or Tachometer |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E311366 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CTT-AN-D24.pdf>
See store item page for other formats.