

# CUR-12G Cut Sheet



Iboco connector, liquid-tight, 90-degree, 3/8in trade size, G3/8 BSPP thread type, gray. Package of 25. For use with I-Flex electrical tubing. Seal gaskets included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CUR-12G>

## Technical Specifications

Brand	Iboco
Item	Connector
Liquid-tight	Yes
Connector Type	90-degree
Material	Non-metallic
Trade Size	3/8in
Thread Type	G3/8 BSPP
Quantity per Pack	25
For Use With	I-Flex electrical tubing
Includes	Seal gaskets

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E311916
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/CUR-12G.pdf>  
See store item page for other formats.