

CUR-12K Cut Sheet

Iboco connector, liquid-tight, 90-degree, 3/8in trade size, G3/8 BSPP thread type, black. Package of 25. For use with I-Flex electrical tubing. Seal gaskets included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CUR-12K>

Technical Specifications

Brand	Iboco
Item	Connector
Liquid-tight	Yes
Connector Type	90-degree
Material	Non-metallic
Trade Size	3/8in
Thread Type	G3/8 BSPP
Quantity per Pack	25
For Use With	I-Flex electrical tubing
Includes	Seal gaskets

Agency Approvals

UL Listed File #	None
UL Recognized File #	E311916
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CUR-12K.pdf>
See store item page for other formats.