

# CVR-438D2-HL Cut Sheet



NITRA pneumatic manual valve, 4-port (4-way), 3-position, center closed, 4in handle, detented, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), Cv=0.89, through panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CVR-438D2-HL>

## Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air or inert gas
Valve Type	Manual directional control
Port Quantity	4-port (4-way)
Number Of Positions	3
Valve Configuration	Center closed
Operator Type	4in handle
Action	Detented
Mounting	Through panel
Inlet Port	1/4in female NPT
Outlet Port	1/4in female NPT
Flow Coefficient	0.89

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/CVR-438D2-HL.pdf>  
See store item page for other formats.