

CVR-447D4-HL Cut Sheet



NITRA pneumatic manual valve, 4-port (4-way), 2-position, 4in handle, detented, 1/2in female NPT inlet(s), 1/2in female NPT outlet(s), Cv=5.29, through panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CVR-447D4-HL>

Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air or inert gas
Valve Type	Manual directional control
Port Quantity	4-port (4-way)
Number Of Positions	2
Operator Type	4in handle
Action	Detented
Mounting	Through panel
Inlet Port	1/2in female NPT
Outlet Port	1/2in female NPT
Flow Coefficient	5.29

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CVR-447D4-HL.pdf>
See store item page for other formats.