

# CVS-527D2-FP Cut Sheet



NITRA pneumatic manual valve, 5-port (4-way), 2-position, locking foot pedal, detented, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), Cv=0.8.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CVS-527D2-FP>

## Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air or inert gas
Valve Type	Manual directional control
Port Quantity	5-port (4-way)
Number Of Positions	2
Operator Type	Locking foot pedal
Action	Detented
Inlet Port	1/4in female NPT
Outlet Port	1/4in female NPT
Stackable	No
Flow Coefficient	0.8
Includes	Guard

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/CVS-527D2-FP.pdf>  
See store item page for other formats.