

# CVU10N Cut Sheet



NITRA pneumatic threaded fitting, check valve, nickel-plated brass body, nickel-plated brass threads, (2) #10-32 female threaded connection(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CVU10N>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Pneumatic Threaded Fitting
<b>Fitting Type</b>	Check valve
<b>Body Material</b>	Nickel-plated brass
<b>Thread Material</b>	Nickel-plated brass
<b>Port Connection Info</b>	(2) #10-32 female threaded
<b>Operating Pressure</b>	125 psi
<b>Operating Temperature</b>	-20 to 160 deg F

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>