

CVU14 Cut Sheet



NITRA pneumatic push-to-connect fitting, check valve, thermoplastic (PBT) body, (1) 1/4in push-to-connect to (1) 1/4in push-to-connect. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CVU14>

Technical Specifications

| | |
|--------------------------------|---------------------|
| Brand | NITRA |
| Item | Fitting |
| Working Fluid | Air or inert gas |
| Fitting Connection Type | Push-to-connect |
| Fitting Type | Check valve |
| Body Material | Thermoplastic (PBT) |
| Thread Sealant | No |

| | |
|---------------------------------|---|
| Fitting Measurement Type | SAE |
| Connection | (1) 1/4in push-to-connect to (1) 1/4in push-to-connect |
| Operating Pressure | -29.5in Hg to 150 psi |
| Operating Temperature | 32-140 °F |
| Quantity per Pack | 5 |
| For Use With | Flexible pneumatic tubing |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |