

CVU38-P Cut Sheet



HydroMode potable water push-to-connect fitting, union straight check valve, acetal body, (2) 3/8in tube connection(s), NSF/ANSI 61. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CVU38-P>

Technical Specifications

Brand	HydroMode
Item	Potable water Push-to-connect Fitting
Fitting Type	Union straight check valve
Body Material	Acetal
Port Connection Info	(2) 3/8in tube
Operating Pressure	145 psi
Operating Temperature	32 to 158 deg F
Agency Approval	NSF/ANSI 61
Quantity per Pack	2

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document