

CWB25-11-30D15 Cut Sheet



WEG Electric CWB series IEC contactor, 25A, (3) N.O. power poles, (1) N.O./ (1) N.C. auxiliary contacts, 120 VAC (50/60Hz) coil voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CWB25-11-30D15>

Technical Specifications

Brand	WEG Electric
Item	Contactor
Series	CWB
Contactor Type	IEC
Actuator Type	Magnetic
Amperage Rating	25A
Power Poles	(3) N.O.
Auxiliary Contacts	(1) N.O./ (1) N.C.
Coil Voltage	120 VAC (50/60Hz)
Horsepower Rating	15hp
SCCR Rating	5kA SCCR
UL Rating	UL 508 rated
Mounting	35mm DIN rail or panel

Agency Approvals

UL Listed File #	E202315
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CWB25-11-30D15.pdf>
See store item page for other formats.