

CWB38-11-30D39 Cut Sheet



WEG Electric CWB series IEC contactor, 38A, (3) N.O. power poles, (1) N.O./ (1) N.C. auxiliary contacts, 480 VAC (50/60Hz) coil voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CWB38-11-30D39>

Technical Specifications

| | |
|--------------------|------------------------|
| Brand | WEG Electric |
| Item | Contactor |
| Series | CWB |
| Contactor Type | IEC |
| Actuator Type | Magnetic |
| Amperage Rating | 38A |
| Power Poles | (3) N.O. |
| Auxiliary Contacts | (1) N.O./ (1) N.C. |
| Coil Voltage | 480 VAC (50/60Hz) |
| Horsepower Rating | 25hp |
| SCCR Rating | 5kA SCCR |
| UL Rating | UL 508 rated |
| Mounting | 35mm DIN rail or panel |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E202315 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/CWB38-11-30D39.pdf>
See store item page for other formats.