


# CWB65-11-30V24 Cut Sheet



WEG Electric CWB series IEC contactor, 65A, (3) N.O. power poles, (1) N.O./1 N.C. auxiliary contacts, 208-240 VAC (60Hz)/180-208 VAC (50Hz) coil voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CWB65-11-30V24>

## Technical Specifications

Brand	WEG Electric
Item	Contactor
Series	CWB
Contactor Type	IEC
Actuator Type	Magnetic
Amperage Rating	65A
Power Poles	(3) N.O.
Auxiliary Contacts	(1) N.O./1 N.C.
Coil Voltage	208-240 VAC (60Hz)/180-208 VAC (50Hz)
Horsepower Rating	50hp
SCCR Rating	5kA SCCR
UL Rating	UL 508 rated
Mounting	35mm DIN rail or panel

## Agency Approvals

UL Listed File #	E202315
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/CWB65-11-30V24.pdf>  
See store item page for other formats.