

# CWBN2-11-30D15 Cut Sheet



WEG Electric CWBN series IEC contactor, NEMA size 2, 50A, (3) N.O. power poles, (1) N.O./ (1) N.C. auxiliary contacts, 120 VAC (50/60Hz) coil voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CWBN2-11-30D15>

## Technical Specifications

Brand	WEG Electric
Item	Contactors
Series	CWBN
Contactors Type	IEC
Actuators Type	Magnetic
Reversing	No
NEMA Size	2
Amperage Rating	50A

Power Poles	(3) N.O.
Auxiliary Contacts	(1) N.O./ (1) N.C.
Coil Voltage	120 VAC (50/60Hz)
Horsepower Rating	25 hp
SCCR Rating	5 kA SCCR
UL Rating	UL 60947 rated
Mounting	35mm DIN rail or panel

## Agency Approvals

UL Listed File #	E202315
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/CWBN2-11-30D15.pdf>  
See store item page for other formats.