

CX5-AP-1A Cut Sheet



AutomationDirect photoelectric sensor, rectangular, plastic, diffuse with background suppression, 15-150mm sensing distance, light-on, PNP, potentiometer, 500 Hz switching frequency, 6.5ft/2m cable length, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CX5-AP-1A>

Technical Specifications

Brand	AutomationDirect	Switching Output	PNP
Item	Photoelectric sensor	Sensing Distance	15-150mm
Shape	Rectangular	Sensitivity	Potentiometer
Housing Size	30 x 15 x 30mm	Operation Mode	Light-on
IP Rating	IP65	Switching Frequency	500 Hz
Housing Material	Plastic	Light Emission	Visible red
Sensing Method	Diffuse with background suppression	Cable Length	6.5ft/2m
Operating Voltage	10-36 VDC	Connection	Pigtail
Number of Wires	3	Conductor Size	26 AWG

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document