

CXP-AP-1F Cut Sheet



AutomationDirect photoelectric sensor, rectangular, polarized retroreflective, visible red, 2m sensing distance, dark-on, PNP, potentiometer, 3-wire, 3-pin M8 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CXP-AP-1F>

Technical Specifications

Brand	AutomationDirect	Switching Output	PNP
Item	Photoelectric sensor	Sensing Distance	2m
Shape	Rectangular	Sensitivity	Potentiometer
Housing Size	30 x 15 x 30mm	Operation Mode	Dark-on
IP Rating	IP65	Switching Frequency	1 kHz
Housing Material	Plastic	Light Emission (NP)	Visible red
Sensing Method	Polarized retroreflective	Connection	3-pin M8 quick-disconnect
Operating Voltage	10-36 VDC	Additional Information	Purchase cable separately
Number of Wires	3		

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document