

CXR-AP-1A Cut Sheet



AutomationDirect photoelectric sensor, rectangular, plastic housing, through-beam receiver, 6m sensing distance, 10-36 VDC operating voltage, dark-on, PNP, 3-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CXR-AP-1A>

Technical Specifications

Brand	AutomationDirect	Switching Output	PNP
Item	Photoelectric sensor	Sensing Distance	6m
Shape	Rectangular	Sensitivity	Potentiometer
Housing Size	30 x 15 x 30mm	Operation Mode	Dark-on
IP Rating	IP65	Switching Frequency	1 kHz
Housing Material	Plastic	Cable Length	6.5ft/2m
Sensing Method	Through-beam receiver	Connection	Pigtail
Operating Voltage	10-36 VDC	Conductor Size	26 AWG
Number of Wires	3		

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document