

CXR-AP-1F Cut Sheet



AutomationDirect photoelectric sensor, rectangular, plastic housing, through-beam receiver, 6m sensing distance, 10-36 VDC operating voltage, dark-on, PNP, 3-wire, 3-pin M8 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CXR-AP-1F>

Technical Specifications

Brand	AutomationDirect	Number of Wires	3
Item	Photoelectric sensor	Switching Output	PNP
Shape	Rectangular	Sensing Distance	6m
Housing Size	30 x 15 x 30mm	Sensitivity	Potentiometer
IP Rating	IP65	Operation Mode	Dark-on
Housing Material	Plastic	Switching Frequency	1 kHz
Sensing Method	Through-beam receiver	Connection	3-pin M8 quick-disconnect
Operating Voltage	10-36 VDC	Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document