

D0-10ND3F Cut Sheet



DirectLOGIC DL05/06 discrete input module, 10-point, 12-24 VDC, sinking/sourcing, fast response, 2 isolated common(s), 5 point(s) per common. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D0-10ND3F>

Technical Specifications

Brand	DirectLOGIC
Item	Input module
I/O Module Type	Discrete
Series	DL05/06
Number of Input Points	10
Nominal Input Voltage	12-24 VDC
Discrete Input Type	Sinking/sourcing
Fast Response	Yes
Number of Isolated Input Commons	2
Number of Points per Common	5
Includes	Removable terminal block
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document