


# D0-10TD2 Cut Sheet



DirectLOGIC DL05/06 discrete output module, 10-point, 12-24 VDC, sourcing, 2 common(s), 5 point(s) per common, 0.3A/point, 1.5A/common. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D0-10TD2>

## Technical Specifications

Brand	DirectLOGIC
Item	Output module
I/O Module Type	Discrete
Series	DL05/06
Number of Output Points	10
Nominal Output Voltage	12-24 VDC
Discrete Output Type	Sourcing
Number of Non-Isolated Output Commons	2
Number of Points per Common	5
Load Current	0.3A/point, 1.5A/common
Fuse Type	User-supplied external fuse
Includes	Removable terminal block
Programming Software	DirectSOFT programming software v4.0 or later

## Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	E200031
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>