

D010 Cut Sheet



Marathon standard efficiency AC induction motor, pressure washer definite purpose, 1hp, 1-phase, 115/208-230 VAC, 3600rpm, ODP, NEMA 56 frame, rolled steel, rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D010>

Technical Specifications

| | |
|--------------------------|----------------------------------|
| Brand | Marathon |
| Item | Motor |
| Efficiency Group | Standard efficiency |
| Efficiency | 72 |
| Voltage Type | AC |
| Motor Type | Induction |
| Motor Application | Pressure washer definite purpose |
| Horsepower Rating | 1hp |
| Number of Phases | 1 |
| Voltage Rating | 115/208-230 VAC |
| Synchronous Speed | 3600rpm |
| Nameplate RPM | 3450rpm |
| Overload Type | Manual |
| Enclosure Type | ODP |

| | |
|---------------------------------|--------------------------------|
| Shaft Type | Round with square key |
| Shaft Diameter | 5/8in |
| Shaft Material | 1144 Stressproof (C-223) steel |
| Motor Frame | NEMA 56 |
| Frame Material | Rolled steel |
| Electrically Reversible | Yes |
| Insulation Class | Class B |
| IP Rating | IP22 |
| Service Factor | 1.15 |
| Integrated Brake | No |
| Junction Box Orientation | F1 |
| Mounting | Rigid base |
| Mounting Orientation | Horizontal |
| Manufacturer Part Number | 056B34D2029 |

Agency Approvals

| | |
|-----------------------------|----------------------------------------|
| UL Listed File # | None |
| UL Recognized File # | E49747 |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | LR2025 |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/D010.pdf>
See store item page for other formats.