

# D2-04TD1 Cut Sheet



DirectLOGIC DL205 discrete output module, 4-point, 12-24 VDC, sinking, 1 common(s), 4 point(s) per common, 4A/point, 8A/module. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D2-04TD1>

## Technical Specifications

|  |   |
|--|---|
| <b>Brand</b>                                 | DirectLOGIC                                   |
| <b>Item</b>                                  | Output module                                 |
| <b>I/O Module Type</b>                       | Discrete                                      |
| <b>Series</b>                                | DL205   |
| <b>Number of Output Points</b>               | 4   |
| <b>Nominal Output Voltage</b>                | 12-24 VDC                                     |
| <b>Discrete Output Type</b>                  | Sinking                                       |
| <b>Number of Non-Isolated Output Commons</b> | 1   |
| <b>Number of Points per Common</b>           | 4   |
| <b>Load Current</b>                          | 4A/point, 8A/module                           |
| <b>Fuse Type</b>                             | Non-replaceable fuse                          |
| <b>Includes</b>                              | Removable terminal block                      |
| <b>Programming Software</b>                  | DirectSOFT programming software v4.0 or later |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E157382                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | see CSA                                |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 234884                                 |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |