D224160DT-M Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

NITRA pneumatic cylinder, heavy duty NFPA tie rod, 1-1/2in bore, 5/8in rod diameter, 16in stroke, double acting, magnetic piston, tapped end caps mount.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/D224160DT-M

Technical Specifications

Brand	NITRA
Item	Cylinder
Working Fluid	Air or inert gas
Cylinder Type	Heavy duty NFPA tie rod
Bore Diameter	1-1/2in
Stroke	16in
Port Size	1/4in female NPT
Mounting	Tapped end caps
Action Type	Double acting

Magnetic Piston	Yes
Adjustable Cushions	No
Body Material	Aluminum
End Cap Material	Aluminum
Rod Material	Chrome-plated steel
Rod Diameter	5/8in
Rod Thread Size	7/16-20 UNF
Maximum Operating Pressure	250 psi

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/D224160DT-M.pdf
See store item page for other formats.