

D240030DT-MC Cut Sheet



NITRA pneumatic cylinder, heavy duty NFPA tie rod, 2-1/2in bore, 5/8in rod diameter, 3in stroke, double acting, magnetic piston, adjustable cushions, tapped end caps mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D240030DT-MC>

Technical Specifications

Brand	NITRA
Item	Cylinder
Working Fluid	Air or inert gas
Cylinder Type	Heavy duty NFPA tie rod
Bore Diameter	2-1/2in
Stroke	3in
Port Size	1/4in female NPT
Mounting	Tapped end caps
Action Type	Double acting

Magnetic Piston	Yes
Adjustable Cushions	Yes
Body Material	Aluminum
End Cap Material	Aluminum
Rod Material	Chrome-plated steel
Rod Diameter	5/8in
Rod Thread Size	7/16-20 UNF
Maximum Operating Pressure	250 psi

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/D240030DT-MC.pdf>
See store item page for other formats.