

D252240DT-MC Cut Sheet

NITRA pneumatic cylinder, heavy duty NFPA tie rod, 3-1/4in bore, 1in rod diameter, 24in stroke, double acting, magnetic piston, adjustable cushions, tapped end caps mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D252240DT-MC>

Technical Specifications

Brand	NITRA
Item	Cylinder
Working Fluid	Air or inert gas
Cylinder Type	Heavy duty NFPA tie rod
Bore Diameter	3-1/4in
Stroke	24in
Port Size	3/8in female NPT
Mounting	Tapped end caps
Action Type	Double acting

Magnetic Piston	Yes
Adjustable Cushions	Yes
Body Material	Aluminum
End Cap Material	Aluminum
Rod Material	Chrome-plated steel
Rod Diameter	1in
Rod Thread Size	3/4-16 UNF
Maximum Operating Pressure	250 psi

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/D252240DT-MC.pdf>
See store item page for other formats.