

D316 Cut Sheet



Marathon standard efficiency AC induction motor, general purpose and 4-in-1, 3hp, 1-phase, 208-230 VAC, 3600rpm, TEFC, 56HC frame, rolled steel, C-face/removable rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D316>

Technical Specifications

Brand	Marathon
Item	Motor
Efficiency Group	Standard efficiency
Efficiency	84
Voltage Type	AC
Motor Type	Induction
Motor Application	General purpose and 4-in-1
Horsepower Rating	3hp
Number of Phases	1
Voltage Rating	208-230 VAC
Synchronous Speed	3600rpm
Nameplate RPM	3450rpm
Overload Type	None
Enclosure Type	TEFC
Shaft Type	Round with square key

Shaft Diameter	5/8in
Shaft Material	1144 Stressproof (C-223) steel
Motor Frame	56HC
Frame Material	Rolled steel
Electrically Reversible	Yes
Insulation Class	Class B
IP Rating	IP43
Service Factor	1.15
Integrated Brake	No
NEMA Design	Design N
Junction Box Orientation	F1
Mounting	C-face/removable rigid base
Mounting Orientation	Horizontal
Manufacturer Part Number	056B34F5328

Agency Approvals

UL Listed File #	None
UL Recognized File #	E49747
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR2025
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document